





	D1,D2,C1,C2; NO/NC			L1 ,L2, L3
	3RV1901-1	3RV1901-2		
$\varnothing 5 \dots 6 \text{ mm} / \text{PZ2}$	0,8 ... 1,2 Nm 7 to 10.3 LB.IN	----		4 ... 6 Nm 35 ... 53 LB.IN
	2 x 0,5 ... 1,5 mm ² 2 x 0,75 ... 2,5 mm ²	2 x 0,5 ... 2,5 mm ²		2 x 2,5 ... 16 mm ²
	2 x 0,5 ... 2,5 mm ²	2 x 0,5 ... 1,5 mm ²		2 x 2,5 ... 35 mm ² 1 x 2,5 ... 50 mm ²
----	----	----		2 x 2,5 ... 50 mm ² 1 x 2,5 ... 70 mm ²
AWG	2 x 18 to 14	2 x 18 to 14	AWG	2 x 10 to 1/0 1 x 10 to 2/0

3RV1901-2.

