



ONE PART FORMED CONTACTS

- Low cost contacts for non critical applications
- Made from copper alloy with a tin plating
- Integral contact and retention spring
- Available in reels of 3000 or loose in bags of 100
- Full support tooling available

Size 20 to 24 with insulation grip



Size 16 with insulation grip




Contact Size AWG	Wire Range mm ²	Insulation diameter	Strip length	Contact description	Order Code Pack of 100	Order Code Reel of 3000
24	.08	.89 (.035)	3.95 (.155) ± 0.25 (.009)	Pin	192922-1370	192990-2580
	.41	1.58 (.062)		Socket	192922-1380	192990-2610
20	.30	1.17 (.046)		Pin	192922-1390	192990-2570
	.75	2.08 (.081)		Socket	192922-1400	192990-2600
16	.50	2.00 (.078)		Pin	192922-1410	192990-2560
	1.50	3.00 (.118)		Socket	192922-1420	192990-2590


TWO PART FORMED CONTACTS

- Three plating styles available
- Separate retention spring
- Up to 200 mating cycles
- Wide range of wire sizes
- Full support tooling available


Size 14 no insulation grip



Size 20 to 26 with insulation grip



Size 16 with insulation grip



Contact Size AWG	Wire Range mm ²	Insulation diameter	Contact description	Order Code Pack of 100 Tin plating	Order Code Pack of 100 Gold flash	Order Code Pack of 100 Plating Code Y	Order Code Reel of 3000 Tin plating	Order Code Reel of 3000 Gold flash	Order Code Reel of 3000 Plating Code Y
24	.08	.89 (.035)	Pin	192990-0020	192990-0080	192900-0448	192990-2510	192990-2650	192900-0406
	.41	1.58 (.062)	Socket	192990-0030	192990-0090	192900-0452	192990-2550	192990-2690	192900-0410
20	.30	1.17 (.046)	Pin	192990-0040	192922-1460	192900-0447	192990-2500	192990-2640	192900-0405
	.75	2.08 (.081)	Socket	192990-0050	192922-1470	192900-0451	192990-2540	192990-2680	192900-0409
16	.50	2.00 (.078)	Pin	192990-0060	192990-0100	192900-0446	192990-2490	192990-2630	192900-0404
	1.50	3.00 (.118)	Socket	192990-0070	192990-0110	192900-0450	192990-2530	192990-2670	192900-0408
14	1.50	No ins. grip	Pin	192990-1240	192990-1220	192900-0445	192990-2480	192990-2620	192900-0403
	2.50		Socket	192990-1250	192990-1230	192900-0449	192990-2520	192990-2660	192900-0407