



Drawings not to scale
All dimensions in mm

SPECIFICATION

CONTACT FORM/STYLE		Open
SWITCHING VOLTAGE	Max. Vac	470
SWITCHING CURRENT	Max. A	0.5
SWITCHING CAPACITY	Max. VA	10
CONTACT RESISTANCE	Max. mΩ	150
SWITCHING DISTANCE	Min. mm	Dependant on magnet
OPERATING TEMPERATURE	Deg. °C	-20° +70°
STORAGE TEMPERATURE	Deg. °C	-25° +70°
CASE MATERIAL		Polypropylene

PRODUCT GROUP TSS134/1

PROXIMITY SENSORS

PART NUMBER

PPS 470

Rev. No.	Revision Note	Date	Signature
A	FIRST ISSUE	10.6.97	P.P.



BS5750/ISO 9000
Reg. No. FM 21080