



Certificate of Compliance

Certificate Number: LR 12730-377
KEMA Ref. 97.3344

Revision: LR 12730-377

Date Issued: August 20, 1997

Issued To: Siemens AG
Abt. ASI 2 GWA TPA
Werner von Siemens
Strasse 48
92220 AMBERG
Germany

The products listed below are eligible to bear the CSA Mark.

Issued By: J. Pankowski
CSA Montreal

Signature

PRODUCTS

Manual Motor Controller, Types 3RV1041, 3RV1341, open type, 3-pole, for across-the-line starting and stopping motors, integral ambient compensated, non replaceable thermal trip features and suitable for providing overload protection. The trip current is 125 percent of the FLA shown on dial.

RATINGS:

General purpose rating
600 Vac, 99 A, FLA max 99 A.

Voltage	Horsepower	
	1-ph	3-ph
115 V		7½ hp
200 V		20 hp
230 V		20 hp
460 V		--
575 V		--
600 V		--