



OMOLOGAZIONI APPROVALS

ENTE : C. S. A.

BODY :

Simbolo :

Symbol :



Riconosciuto conforme alle norme : CSA Standard C 22.2 No 0 - M.
In accordance to standards : CSA Standard C 22.2 No 0.4 - M.
CSA Standard C 22.2 No 14 - M.
CSA Standard C 22.2 No 94.

TIPO TYPE	Corrente nominale Nominal current Tensione nominale Nominal voltage	Vita elettrica a pieno carico in AC 1(cicli) Electrical life At AC 1 rated load (cycles)	Portata Motore Motor rating	Temperatura Ambiente Ambient temperature	N. file
40.31	10 A - 250 Vac	100 · 10 ³	1/3 Hp - 250 Vac	85°C	C N : 028197 0 000
40.51	10 A - 250 Vac	100 · 10 ³	1/3 Hp - 250 Vac	85°C	C N : 028197 0 000
40.52	5 A - 250 Vac	100 · 10 ³	1/6 Hp - 250 Vac	85°C	C N : 028197 0 000
40.61	15 A - 250 Vac	100 · 10 ³	1/2 Hp - 250 Vac	85°C	C N : 028197 0 000

missione LO	Livello di revisione nr. 0	DATA REVISIONE 08.06.1999	PAGINA NR. 3/14
approvazione UT			