



FEATURES:

- Converts BNC (Male) cables/connectors to Minigator test clips for test versatility.
- BNC connector is molded directly to the wire for pull strength durability and dust/moisture resistance.
- BNC dielectric is PTFE for superior temperature performance
- BNC center contact is gold plated Beryllium Copper for corrosion resistance, low contact resistance and long insertion life.
- Minigators attach to terminals up to .187" (4,75mm)

MATERIALS:

BNC: Body - Brass, Nickel Plated

Center Contact – Beryllium Copper, Gold Plated.

Dielectric: PTFE

Wire: 20 AWG, Stranding 41 x 36 T.C., PVC Insulated, .087" (2,21 mm) O.D., Color matches alligator boots.

Marking: "POMONA 2631"

Minigators: Body – Steel, Nickel Plated

Spring- Stainless Steel

Flex Boot - Vinyl

RATINGS:

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 150VRMS Max.

Operating Temperature: +50°C (+122°F) Max.

ORDERING INFORMATION: Model 2631

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA