

The new hand-held enclosure system for data acquisition and instrumentation in mobile applications.

**Mountable components:**

Chip card/magnetic card readers, scanners, PCMCIA interfaces, displays, membrane keypads, switching mat sets, plug connectors, socket connectors etc..

**Product line:**

- Taguan 130 flat
- Taguan 130 deep
- Taguan 180
- Taguan 230



**Technical data**

**Enclosure**

- Material : ABS
- Colour: similar to RAL 5020 green-blue
- Ingress protection: IP40 to EN 60529
- Surface resistance: 4 x 10<sup>14</sup> Ohm to DIN 53482
- Disruptive strength: 24KV/mm to DIN 53481
- Flammability: HB to UL 94
- Temperature resistance: -40°C to +80°C

**Dimensions:**

Enclosure body:	Display cut-out	
Taguan 130 flat	125x80/70x36,7mm	45x17,4mm
Taguan 130 deep	125x80/70x46,7mm	45x17,4mm
Taguan 180	180x84/70x52,5mm	56x33mm
Taguan 230	229x97/70x52,5mm	66x43mm

**Accessories:**

- Membrane keypads
- Switching mat sets
- Battery holders
- Battery compartment, empty
- Battery pack
- Battery charging station
- Spring contacts
- Head panels
- Shaft panels
- Variable display fixing set
- Hand strap
- Wrist strap
- Clip
- NEW! Docking Station

