

Professionally approved products. Datasheet

0673 Brass, Sintered Bronze 12bar Pneumatic Silencer, Threaded, M5 x 0.8 Male

RS Stock number 722-261



0673 THREADED SILENCER, BSP PARALLEL, METRIC AND UNF

| | | | |
|--------------------------|------------------------------------|-------------------------------------|----------------------------------|
| maximum working pressure | bar 12 | MPa 1,2 | psi 174 |
| working temperature | °C (Celsius) From -20 to 150 | F (Fahrenheit) From -4 to 302 | K (Kelvin) From 253 to 423 |
| body | brass | | |
| sub-base | brass | | |
| silencer | sintered bronze | | |

| | | C | E (mm) | F (mm) | H (mm) | (kg) |
|--|------------|--------|-----------|-----------|-----------|-------|
| | 0673 00 10 | G1/8 | 8,0 | 14,0 | 14,0 | 0,007 |
| | 0673 00 13 | G1/4 | 8,0 | 17,0 | 14,0 | 0,011 |
| | 0673 00 17 | G3/8 | 10,0 | 22,0 | 17,0 | 0,017 |
| | 0673 00 19 | M5x0,8 | 4,0 | 7,0 | 8,0 | 0,002 |
| | 0673 00 20 | 10-32 | 5,0 | 7,0 | 12,0 | 0,007 |
| | 0673 00 21 | G1/2 | 12,0 | 27,0 | 21,0 | 0,027 |



Flow rates for 0670 silencers in NI/hr (Normal litres per hour)

| RS S/N | LEGRIS P/N | 2 Bar | 4 Bar | 6 Bar |
|---------|------------|-------|-------|-------|
| 722-261 | 0670 0019 | 41.7 | 89.7 | 139 |
| 722-277 | 0670 0010 | 217 | 436 | 641 |
| 722-283 | 0670 0013 | 689 | 1306 | 1914 |
| - | 0670 0017 | 1596 | 2384 | 3388 |
| - | 0670 0021 | 2159 | 3747 | 5300 |
| - | 0670 0027 | 3887 | 6130 | 8523 |
| - | 0670 0034 | - | - | - |