

ENTE : RINA
BODY :

Simbolo : RINA
Symbol :

Riconosciuto conforme alle norme : EN 61810-1:1998 , EN 61810-5:1998 , EN 60255-23:1996
In accordance to standards :

TIPO TYPE	Corrente nominale Nominal current Tensione nominale Nominal voltage	Vita elettrica a pieno Carico in AC1 (cicli) Electrical life at AC1 rated load (cycles)	Portata motore Motor rating	Temperatura ambiente Ambient temperature	N. File
55.X2 - X3	10 A - 250 Vac	100.000	/	85 °C	ELE51703CS/1
55.X4	7 A - 250 Vac				

ENTE : SEMKO
BODY :

Simbolo :
Symbol :



Riconosciuto conforme alle norme : IEC 61810-1: Table 3 - Type test with
In accordance to standards : IEC 61058-1:1992+A1:1993 (IEC 61058-1:1990+
A1:1993+A2:1994)
IEC 61095:1993+A11 (IEC 61095:1992)

TIPO TYPE	Corrente nominale Nominal current Tensione nominale Nominal voltage	Vita elettrica a pieno Carico in AC1 (cicli) Electrical life at AC1 rated load (cycles)	Portata motore Motor rating	Temperatura ambiente Ambient temperature	N. File
55.X2 - X3	10 A - 250 Vac	50.000	/	85 °C	001 1007/01
55.X4	5 A - 250 Vac				