

**ENTE :  
BODY****American Bureau of Shipping (ABS)****Simbolo :  
Symbol :****Riconosciuto conforme alle norme :  
In accordance to standards :**ABS Rules: SVR 2003 1-1-4/3.7, 4-8-3/1.11, 4-8-3/5  
Other Standard: UL 508 – UL File E106390

TIPO <i>TYPE</i>	Corrente nominale <i>Nominal current</i> Tensione nominale <i>Nominal voltage</i>	Vita elettrica a pieno Carico in AC1 (cicli) <i>Electrical life at AC1 rated load (cycles)</i>	Portata motore <i>Motor rating</i>	Temperatura ambiente <i>Ambient temperature</i>	N. File
55.X2 – X3	10 A – 250 Vac	/	/	40 °C	03-GE-349203-PDA
55.X4	7 A – 250 Vac				

**ENTE :  
BODY :****Biuro Badawcze ds. Jakości (BBJ)****Simbolo :  
Symbol :****Riconosciuto conforme alle norme :  
In accordance to standards :**

/

TIPO <i>TYPE</i>	Corrente nominale <i>Nominal current</i> Tensione nominale <i>Nominal voltage</i>	Vita elettrica a pieno Carico in AC1 (cicli) <i>Electrical life at AC1 rated load (cycles)</i>	Portata motore <i>Motor rating</i>	Temperatura ambiente <i>Ambient temperature</i>	N. File
55.X2 – X3	10 A – 250 Vac	/	/	/	B/12/1651/01
55.X4	5 A – 250 Vac				