

# 107 Electronic Installation Buzzer

Signal device for the 22.5 mm control panel programme  
Low current consumption  
High protection rating IP 65



## TECHNICAL SPECIFICATIONS

---

**Dimensions**  
(Diameter x Height):  
28,2 mm x 68,8 mm

**Fixing :**  
Installation mounting for 22.5 mm Ø (M 22);

**Housing :**  
PA - GF, black;

**Connection:**  
Connector plug with screwable connection max. 1.5 mm<sup>2</sup>;

**Current consumption:**  
<= 8 mA

**Volume :**  
min. 80 dB (A) / 10 cm;

**Duty cycle:**  
100 %;

**Audio frequency:**  
2400 Hz;

**Tone type:**  
Continuous or pulse tone with approx. 1 Hz;

**Life duration:**  
> 5.000 h;

