

Article

2477 PJO 075 P30



Technical Data

Wheel diameter	75 mm
Width of Tread	25 mm
Centre hole	11 mm
Offset	24 mm
Swept radius-Ø	160 mm
Dynamic Load capacity	75 Kg / daN
Static Load capacity	188 Kg / daN
Temperature	- 20 / + 60 °C
Norm	EN 12530
Overall height	100 mm

Description

Swivel Castor with total lock, housing made of zinc-chromatised pressed steel, double ball bearing swivel head, wheel made of Polypropylene, tread made of thermoplastic rubber, plain bearing, single bolt hole.

