

Combination pH Electrode and Conductivity Probe for HI 9812 and HI 9813

Code		HI 1285
Body		Polypro
Reference	Junction	single
	Cell	gel
Junction	Type	fiber
Tip	Shape	sphere
	Dimension	Ø5.0 mm
Plug	Type	multi-pin
Temp range °C		0/60
Pressure PSI/BAR		7.25/0.5
