

PRECISION WIRE STRIPPER

3757

Specification as 3756 below but adjustable. In 3 sizes, each adjustable to 6 dia.
50mm scale with 1mm graduation. Front hole diameter for all sizes is 2mm/ $\frac{5}{64}$ ".



| SIZE | ADJUST TO: mm /AWG | ITEM NO | | BOX QTY | WEIGHT |
|------|--|---------|--|---------|--------|
| 1 | 0.12/36, 0.16/34, 0.20/32, 0.35/30, 0.30/28, 0.40/26, | T3757 1 | | 3 | 26g |
| 2 | 0.25/30, 0.30/28, 0.40/26, 0.50/240, 0.60/22, 0.80/200, | T3757 2 | | 3 | 26g |
| 3 | 0.30/28, 0.40/26, 0.50/24, 0.60/22, 0.80/20, 1.00/18, | T3757 3 | | 3 | 26g |