


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS					
IJ				P	LTR	DESCRIPTION	DATE	DWN	APVD
				A		INITIAL ISSUE	13 SEP 05	MGR	DB



NOTES:

- 1 ATTENUATION $\leq 0,3$ dB, MEASURED AT 1300nm ACC. TO IEC 874-1
 CLAUSE 4.4.7 METHOD 7 EQUILIBRIUM MODE CONDITION
- 2 INDIVIDUAL LENGTH DIFFERENCE ON BOTH SIDES ≤ 5 mm
- 3 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH
 INDIVIDUALLY PACKED ASSEMBLY
- 4 DAT LABEL INFO:
 - UNIQUE SERIAL NUMBER
 - TYCO LOGO PN
 - MANUFACTURING LOCN.
- 5 BLANK LABEL

6 NON CROSS OVER AS PER BELOW TABLE

LEFT CONN.	RIGHT CONN.
SC CONN. A	SC CONN. B
SC CONN. B	SC CONN. A

7 CABLE INFO:

- CORE DIA - 50/125 μ m
- OUTER DIA - 2,5 mm
- JACKET COLOR - ORANGE
- JACKET MATERIAL - LSZH

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-5349565-Y	XY,0
9-5349565-1	1,5
9-5349565-9	9,5
9-5349565-0	100 -0/+3,0

Qty	Part Number	Description	Item
2	-	FOAC DAT-85 LABEL ON REEL	8
4	-	PROTECTIVE COVER, 2.5MM, BLACK	7
2	-	SC DUPLEX HOUSING, BEAM HALF	6
2	-	SC DUPLEX HOUSING, RET. PLATE HALF	5
4	-	SC CERAMIC, OVERMOLDED	4
4	-	CRIMP EYELET, SC, 2.0MM PLATED	3
4	-	FOAC STRAIN RELIEF, SC/FC BEIGE	2
L	-	FOCAB 2.5 50/125 DUPLEX ORANGE	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GIRIYAPPA M 13 SEP 05	Tyco Electronics Corporation FOBU, Bangalore, India	
DIMENSIONS: mm		CHK DIWAKAR BELAVADI 13 SEP 05	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DIWAKAR BELAVADI 13 SEP 05	PRODUCT SPEC	
0 PLC $\pm -$ 1 PLC $\pm -$ 2 PLC $\pm -$ 3 PLC $\pm -$ 4 PLC $\pm -$ ANGLES $\pm -$		APPLICATION SPEC		
MATERIAL		WEIGHT	SIZE A2	CAGE CODE 00779
FINISH		DRAWING NO C=5349565		RESTRICTED TO
		CUSTOMER DRAWING		SCALE NTS
		SHEET 1 OF 1		REV A