

Product Information

FTP150x50-Ø20 NL60

EAN 4031582329452

Wheel centre made of cast iron, Tread:
Polyurethane, casted, precision ball bearing

Wheel diameter	150 mm
Width of Tread	50 mm
Axle Hole Ø	20 mm
Hub length	60 mm
Temperature	- 20 / + 60 °C
Standard	EN 12533
Weight	3.88 kg
Dynamic Load capacity	700 kg
Static Load capacity	1400 kg
Hardness of tread	A 92 Shore

