

*Comfortable,
strong and durable*

Protwist[®]

Advantages

- ▶ Ergonomic handle
- ▶ Strong, comfortable grip
- ▶ Accurate black-tipped blade
- ▶ Powerful carbon silicon steel blade
- ▶ Colour coded



N ▶ 308

**New
Screwdriver**

Protwist[®]



**CARBON
SILICIUM**

**GOOD TORQUE
TRANSMISSION AND
FAST SCREWING SPEED**

**Natural grip, excellent
comfort**

- Efficient pre-tightening.
- Comfortable high torque action.
- Easier torque transfer.

**Strong, comfortable grip and
long-lasting performance**

Soft polyurethane zone, polyamide core for high resistance to:

- Impact and stress.
- Abrasion and chemical agents.



**Five handle sizes to suit the tip
size**

- Small sizes have a long, thin body for a faster screwing action.
- Larger sizes have a wider gripping surface for a firmer hold and maximum torque transfer.



**Silicon carbon
steel blades**

- Very strong.
- Excellent resistance to bending.

**Black tip : no risk of flaking and
guaranteed accuracy**

- Retains the dimensional accuracy of the machined tip.
- No chromium deposits in the environment.
- No weakening due to hydrogen release during chromium plating.





Choosing the right blade for your needs

The Protwist® range, an ideal combination of blade types and tip patterns to choose from. Over 200 references to cover all your needs.

	Short blade AN	Round blade, sand-blasted tip AS	Round blade, black tip AN	Hexagonal blade AW	Hexagonal blade with bolster AWH	1,000 V insulated blade A.VE	Hexagonal blade AWHH AWSH
	Awkward spaces	Frequent use	Intensive use	High torque	Added torquing power with a wrench	Live working	Hexagon socket heads
	10 refs 7 tips	24 refs 20 tips	90 refs 59 tips	18 refs 14 tips	16 refs 14 tips	31 refs 23 tips	14 refs 7 tips
	4 → 6,5 mm ☞ x 4	2,5 → 10 mm ☞ x 11	2 → 10 mm ☞ x 30	4 → 12 mm ☞ x 10	5,5 → 14 mm ☞ x 8	2 → 12 mm ☞ x 18	
	1 → 2 ☞ x 3	0 → 3 ☞ x 4	0 → 4 ☞ x 10	1 → 4 ☞ x 4	1 → 4 ☞ x 4	0 → 4 ☞ x 5	
	1 → 2 ☞ x 3	0 → 3 ☞ x 4	0 → 4 ☞ x 9	1 → 4 ☞ x 4	1 → 4 ☞ x 4	0 → 3 ☞ x 4	
		10 → 30 ☞ x 5	6 → 40 ☞ x 12				
			10 → 40 ☞ x 7				
			5 → 40 ☞ x 12				
			10 → 40 ☞ x 7				
			1 → 3 ☞ x 3				
						1 → 2 ☞ x 4	
							2 → 8 mm ☞ x 14

Colour coding for immediate identification of all Protwist® screwdrivers.

