



Save as PDF




Peli protector cases - Long cases - 1720 Long Case



Interior dimensions:
106.6 x 34.3 x 13.3 cm (42" x 14" x 5")

Watertight, crushproof, and dust proof

- Easy-open, double-step latches
- Open cell core with solid wall design - strong, light weight
- O-ring seal
- Automatic Pressure Equalization Valve
- Fold down handles
- Strong polyurethane wheels with stainless steel bearings
- Stainless steel hardware and padlock protectors
- 3-piece foam set
- Personalised nameplate service available
- Unconditionally Guaranteed



Black Od_green

Peli protector cases - Long cases - 1720 Long Case SPECIFICATIONS

Exterior Dimensions (L x W x D)		Interior Dimensions (L x W x D)	
112.7 x 40.6 x 15.5 cm (44" x 16" x 6")		106.6 x 34.3 x 13.3 cm (42" x 14" x 5")	
Lid Depth	Bottom Depth	Total Depth	
4.4 cm (2")	8.9 cm (3.50")	13.3 cm (5.25")	
Lid Depth	Bottom Depth	Total Depth	
4.4 cm (1.75")	8.9 cm (3.50")	13.3 cm (5.25")	
Weight w/Foam	Weight w/o Foam	Buoyancy Max.	
8.6 kg. (18.96 lbs)	7.6kg (16.76 lbs.)	73 kg (160.94 lbs.)	
Range Temperature		No. of Wheels	
-40 / 99° C (-40 / 210° F)		2	

Personalized Nameplate Available

1720 Long Case Certificates

- Def Stan 81-41/STANAG 4280

Materials

Body	Latch	Lid O-Ring	Pins
Polypropylene	ABS	PolymerStainless Steel	
Foam	Purge Body	Purge Vent	Purge O-Ring
1.3 lb Polyurethane	ABS	3 Micron Hydrophobic Non-Woven PET	70 Shore Nitrile

Configuration

Cat. #	Description
1720	Peli protector cases - Long cases - 1720 Long Case

Peli protector cases - Long cases - 1720 Long Case Accessories

Cat. #	Description