




Kit Number	SRR-LAB1	SRR-LAB2	SRR-LAB3
Kit Photo			
Part Numbers	<p> SRR3011-4R7YL SRR3011-6R8YL SRR3011-150YL SRR3011-220YL SRR3011-330YL SRR3011-470YL SRR3011-680YL SRR3011-101YL SRR4028-3R3Y SRR4028-5R6Y SRR4028-100Y SRR4028-220Y SRR4028-470Y SRR4028-680Y SRR4028-151Y SRR4028-331Y SRR5028-6R2Y SRR5028-8R2Y SRR5028-150Y SRR5028-220Y SRR5028-390Y SRR5028-820Y SRR5028-221Y SRR5028-681Y SRR6028-5R0Y SRR6028-100Y SRR6028-180Y SRR6028-330Y SRR6028-680Y SRR6028-101Y SRR6028-151Y SRR6028-331Y (3 of each in every labkit) </p>	<p> SRR7032-100M SRR7032-220M SRR7032-470M SRR7032-101M SRR7032-151M SRR7032-221M SRR7032-471M SRR7032-102M SRR7045-150M SRR7045-330M SRR7045-680M SRR7045-121M SRR7045-181M SRR7045-331M SRR7045-681M SRR7045-102M SRR1005-100M SRR1005-220Y SRR1005-390Y SRR1005-680Y SRR1005-151K SRR1005-221K SRR1005-471K SRR1005-681K SRR1806-100M SRR1806-150M SRR1806-330M SRR1806-470M SRR1806-101M SRR1806-151M SRR1806-331M SRR1806-102M (3 of each in every labkit) </p>	<p> SRR1240-4R7M SRR1240-100M SRR1240-150M SRR1240-270M SRR1240-470M SRR1240-121K SRR1240-221K SRR1240-331K SRR1260-100M SRR1260-150M SRR1260-220M SRR1260-470M SRR1260-680M SRR1260-101M SRR1260-151K SRR1260-471K SRR1280-4R7Y SRR1280-100M SRR1280-180M SRR1280-330M SRR1280-560M SRR1280-820M SRR1280-151K SRR1280-271K SRR1210-5R6Y SRR1210-8R2Y SRR1210-270M SRR1210-390M SRR1210-680M SRR1210-121M SRR1210-221M SRR1210-391M (3 of each in every labkit) </p>