

Mill file with 2 flat edges, industry pack, unhandled



1-143...-0

inch/mm/size		
6/150-1	10	1-143-06-1-0
8/200-1	10	1-143-08-1-0
10/250-1	10	1-143-10-1-0
12/300-1	5	1-143-12-1-0

Mill file with 2 flat edges, single pack carded, ERGO® handle



1-143...-2

inch/mm/size		
6/150-1	5	1-143-06-1-2
8/200-1	5	1-143-08-1-2
10/250-1	5	1-143-10-1-2
12/300-1	5	1-143-12-1-2

Square file, industry pack, unhandled



1-160...-0

inch/mm/size		
4/100-1	10	1-160-04-1-0
4/100-2	10	1-160-04-2-0
4/100-3	10	1-160-04-3-0
6/150-1	10	1-160-06-1-0
6/150-2	10	1-160-06-2-0
6/150-3	10	1-160-06-3-0
8/200-1	10	1-160-08-1-0
8/200-2	10	1-160-08-2-0
8/200-3	10	1-160-08-3-0
10/250-1	10	1-160-10-1-0
10/250-2	10	1-160-10-2-0
10/250-3	10	1-160-10-3-0
12/300-1	5	1-160-12-1-0
12/300-2	5	1-160-12-2-0

Square file, single pack carded, ERGO® handle



1-160...-2

inch/mm/size		
4/100-1	5	1-160-04-1-2
4/100-2	5	1-160-04-2-2
6/150-1	5	1-160-06-1-2
6/150-2	5	1-160-06-2-2
6/150-3	5	1-160-06-3-2
8/200-1	5	1-160-08-1-2
8/200-2	5	1-160-08-2-2
8/200-3	5	1-160-08-3-2
10/250-1	5	1-160-10-1-2
10/250-2	5	1-160-10-2-2
10/250-3	5	1-160-10-3-2
12/300-1	5	1-160-12-1-2
12/300-2	5	1-160-12-2-2

Three square file, industry pack, unhandled



1-170...-0

inch/mm/size		
4/100-2	10	1-170-04-2-0
4/100-3	10	1-170-04-3-0
6/150-1	10	1-170-06-1-0
6/150-2	10	1-170-06-2-0
6/150-3	10	1-170-06-3-0
8/200-1	10	1-170-08-1-0
8/200-2	10	1-170-08-2-0
8/200-3	10	1-170-08-3-0
10/250-1	10	1-170-10-1-0
10/250-2	10	1-170-10-2-0
10/250-3	10	1-170-10-3-0
12/300-1	5	1-170-12-1-0
12/300-2	5	1-170-12-2-0

Three square file, single pack carded, ERGO® handle



1-170...-2

inch/mm/size		
4/100-2	5	1-170-04-2-2
6/150-1	5	1-170-06-1-2
6/150-2	5	1-170-06-2-2
6/150-3	5	1-170-06-3-2
8/200-1	5	1-170-08-1-2
8/200-2	5	1-170-08-2-2
8/200-3	5	1-170-08-3-2
10/250-1	5	1-170-10-1-2
10/250-2	5	1-170-10-2-2
10/250-3	5	1-170-10-3-2
12/300-1	5	1-170-12-1-2
12/300-2	5	1-170-12-2-2

Half-round file, industry pack, unhandled



1-210...-0

inch/mm/size		
4/100-1	10	1-210-04-1-0
4/100-2	10	1-210-04-2-0
4/100-3	10	1-210-04-3-0
6/150-1	10	1-210-06-1-0
6/150-2	10	1-210-06-2-0
6/150-3	10	1-210-06-3-0
8/200-1	10	1-210-08-1-0
8/200-2	10	1-210-08-2-0
8/200-3	10	1-210-08-3-0
10/250-1	10	1-210-10-1-0
10/250-2	10	1-210-10-2-0
10/250-3	10	1-210-10-3-0
12/300-1	5	1-210-12-1-0
12/300-2	5	1-210-12-2-0
12/300-3	5	1-210-12-3-0
14/350-1	5	1-210-14-1-0

Half-round file, single pack carded, ERGO® handle



1-210...-2

inch/mm/size		
4/100-1	5	1-210-04-1-2
4/100-2	5	1-210-04-2-2
6/150-1	5	1-210-06-1-2
6/150-2	5	1-210-06-2-2
6/150-3	5	1-210-06-3-2
8/200-1	5	1-210-08-1-2
8/200-2	5	1-210-08-2-2
8/200-3	5	1-210-08-3-2
10/250-1	5	1-210-10-1-2
10/250-2	5	1-210-10-2-2
10/250-3	5	1-210-10-3-2
12/300-1	5	1-210-12-1-2
12/300-2	5	1-210-12-2-2
12/300-3	5	1-210-12-3-2

