

# Rechargeable Working Light



## Cordless LED Worklight

Dual function light comprises inspection light with 51 LEDs for lateral beam and front torch with 9 LEDs

Rubberised housing with swivelling plastic hooks

Status display for indicating charge status

Technical data	
Max. Operating time:	Inspection light 4 h, torch 8 h
Recharge time:	8 h
Light source:	51 x LEDs in 3 rows, 9 x LEDs in the head
Dimensions L x W x H:	400 x 50 x 40 mm

## Supplied with

Rechargeable NiMH 3.6 V / 2 Ah battery block in the handle with charging socket, 1 x mains charger fitted with a European mains plug suitable for Germany and Austria and a 12 Vdc vehicle charger plug and lead.