


# TINI Q-G® ASSEMBLY INSTRUCTIONS

## CORD PLUGS - Series TA(\*)F, TA(\*)FL, TA(\*)JM & TA(\*)ML


To assemble a cord plug, proceed as follows:

1. Strip cable as shown in illustration.
2. Assemble cord plug parts and cable as shown in exploded view of male or female plug. If cable is larger than .115 inch (2.92 mm) outside diameter Series TA(\*)FL or TA(\*)ML (without bushing) should be used.
3. Solder leads (22 AWG maximum) to terminals on insert.
4. Slide insulating spacer forward to interlock into insert. If necessary, rotate spacer to assure interlocking fit.


### CABLE STRIPPING



### EXPLODED VIEW, FEMALE CORD PLUG



### EXPLODED VIEW, MALE CORD PLUG



\* NOT USED ON SERIES TA(\*)ML AND TA(\*)FL.

5. Slide cable clamp forward over spacer. Rotate, if necessary, to assure interlocking fit.  
**NOTE:** Make sure insert, spacer and clamp are properly interlocked and fit tightly together before proceeding. See crimping illustration.
6. Press forward slightly on cable and crimp rear set of ears on clamp. Make sure insert, spacer and clamp stay interlocked and press tightly together as crimping is done. See illustration.
7. Carefully crimp front ears around cable braid. (Crimp rear ears around cable).
8. Push completed assembly into rear of housing. If necessary, rotate assembly to assure nib on clamp fits into slot on housing. See crimping illustration to identify full insertion point of assembly into housing.
9. Slide end cap forward and thread it onto housing for secure, completed plug.

### DETAILS OF CRIMPING

NOTE: WHEN INSERTED INTO HOUSING, INSERT/SPACER/CLAMP SHOULD BE COMPLETELY ASSEMBLED INTO HOUSING TO THIS POINT.

