

F202 A-25/0,03

General Information

Extended Product Type:	F202 A-25/0,03
Product ID:	2CSF202101R1250
EAN:	8012542782506
Catalog Description:	F202 A-25/0,03 Residual Current Dev.
Long Description:	The RCCBs F200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications.

Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » Residual Current Devices RCDs » Residual Current Devices RCDs

Ordering

EAN:	8012542782506
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85363030

Dimensions

Product Net Width:	0.035 m
Product Net Height:	0.085 m
Product Net Depth:	0.069 m
Product Net Weight:	0.200 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	0.041 m
Package Level 1 Height:	0.078 m
Package Level 1 Length:	0.096 m
Package Level 1 Gross Weight:	0.225 kg
Package Level 1 EAN:	8012542782506
Package Level 2 Units:	6 piece
Package Level 2 Gross Weight:	1.35 kg

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-07-01
--------------	--

Additional Information

IIT Publishing Status:	Level 0 - Information enabled
Number of Poles:	2
Operating Characteristic:	Instantaneous
Power Loss:	Per Pole 1 W
Product Main Type:	F200
Product Name:	Residual Current Device
Rated Current (I_n):	25 A
Rated Residual Current:	30 mA
Rated Voltage (U_r):	230/400 V
Standards:	IEC EN 61008
Type of Residual Current:	A type

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	ITSCE116F200
---------------------------------	------------------------------

Classifications

E-nummer:	E2160114
Object Classification Code:	Q
UNSPSC:	39120000