

## Joker Ratcheting combination wrenches

**JOKER**



**Application:** Hexagonal nuts or bolts

**Design:** Ratcheting combination wrench; unique holding function, thanks to the metal plate in the jaw, reduces the risk of dropping nuts and bolts; replaceable metal plate in the jaw secures nuts and bolts with its extra hard teeth and reduces the danger of slipping; integrated limit stop prevents any slipping around the bolt head and allows higher torque to be applied; double-hex geometry makes for a positive connection with nuts or bolts and reduces the risk of slipping; return angle of only 30° at the open end to avoid time consuming flipping of the wrench during fastening jobs; ratchet mechanism at the ring end, with an exceptional, fine-tooth mechanism – 80 teeth in all – enables flexibility in very confined working spaces; specially forged geometry for high torque transfer and strength; high performance chrome molybdenum steel; nickel-chrome coating for high corrosion protection.

Code	mm	mm	mm	mm	mm	mm	mm	
05073270001	10	159	22	5.5	21	7.2	3	
05073273001	13	177	27.3	7	25	8.6	3	
05073277001	17	224	37.2	8.5	32.7	10.5	3	
05073279001	19	246	42	9.5	34.8	11	3	