


EMLP (20X7)R

Order No.: 0819479

The figure shows a similar product



Plastic label, Roll, white, Unlabeled, Can be labeled with: Thermomark R, Thermomark X, Thermomark S, Mounting type: Adhesive, Lettering field: 20 x 7 mm

Commercial data	
EAN	4  046356 159852
Pack	1
Customs tariff	39199000
Gross weight in pieces	117.20 g
Country of Origin	DE
Catalog page information	Page 216 (CL2-2011)

Product notes

WEEE/RoHS-compliant since:
29/09/2006



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data	
General	
Length (b)	20 mm
Width (a)	7 mm
Color	white
Inflammability class according to UL 94	V0
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Ambient temperature (operation)	-40 °C ... 120 °C
Ambient temperature (assembly)	18 °C ... 40 °C
Components	free from silicone and halogen
Material	Polyester
Number of individual labels	500
Number of individual labels per row	4
RoHS compliant	Yes
Halogen-free	Yes
Silicone-free	Yes
Cadmium-free	Yes
Adhesive	Acrylic
Printability	Thermal transfer
Device	5146257 THERMOMARK S1.1
	5146231 THERMOMARK X1.2
	5146477 THERMOMARK ROLL
	5145313 THERMOMARK S1
	5145274 THERMOMARK X1.1
Ink ribbon	5145384 THERMOMARK-RIBBON 110
	0829544 THERMOMARK-RIBBON 110 BU
	0829542 THERMOMARK-RIBBON 110 GN
	0829543 THERMOMARK-RIBBON 110 RD
Test specification weathering-resistance	Following ISO 4892-2:2006-02 + A1:2009-07
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	KFW 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result	Test passed
Burning behaviour	self-extinguishing
Foil strength	175 µm

Adhesive strength	400 µm
-------------------	--------

Certificates

Certification
Certifications applied for:
Certification Ex:

Accessories

Item	Designation	Description
General		
5145384	THERMOMARK-RIBBON 110	Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black

Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG, England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;