

HUBER+SUHNER® DATA SHEET

Coaxial Cable Connector: 11_MBX-50-2-1/113_N

Rev.: E 

Description

Straight cable plug

Interface Standards
HUBER+SUHNER MBX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Centre contact crimped
Outer contact crimped
Weight 0.003546 kg

Environmental Data

Operating Temperature -55 °C to 155 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

Centre contact	Copper Beryllium Alloy
Outer contact	Bronze / Brass
Body	Brass
Insulator	PFA / PTFE
Crimp ferrule	Copper

Surface Plating

SUCOPRO Plating
SUCOPRO Plating
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00162030
Catalogue drawing	DCA-00161650
Assembly instruction	DOC-0000333519

Ordering Information

Bulk 100 pcs package	11_MBX-50-2-1/113_NH
Single package	11_MBX-50-2-1/113_NE

Additional Information

Suitable cables ENVIROFLEX_316_D, K_02252_D, G_02232_D

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions