



Part Number: CW1306-1
Tilt Switch / Motion Sensor
Product Data Sheet

PICTURE



✓ **RoHS Compliant**

OPERATION




FEATURES

- Resistant to Ambient Environmental Conditions
- Housing Material : Tin Plated
- Hermetically Sealed and Inert Gas Filled

DIMENSIONS

Drawings not to scale.
 All dimensions in inches (mm) nominal.



SPECIFICATION

Contact Capacity	0.25 A, 60 V MAX, 3 VA MAX
Contact Resistance	30 Ω MAX
Make Angle	10° Below Horizontal
Break Angle	10° Above Horizontal
Differential Angle	15° MAX
Operating Temperature	-37° to 100°C

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

Phone: (1) 973 777 6900

www.comus-intl.com

Fax: (1) 973 777 8405