

## Sheetsteel housing **BGUK 3**



### Advantages

- Integrated Rail System for the installation of different product sizes
- Excellent corrosion protection and high abrasion resistance through powder-coated surface RAL 5008
- With cooling fins for optimal heat extraction
- Faceplate without cooling fins for individual connection options
- Integrated crane eyes
- Optionally available in degree of protection IP 54

### Approvals



## Sheetsteel housing BGUK 3

Type		BGUK 3
Electrical data	Operating data	
	For power (single phase)	500 VA
	For power (three phase)	400 VA
	Max. Power loss (at 40 °C ambient temperature)	48 W
	Enclosure suitable for protection index	IP 20
Order numbers		
Order Number		BGUK 3

Type		BGUK 3
Mechanical data	Terminal and mounting	
	Floor mounting	No
	Wall mounting	Yes
	Cable glanding type	M20
	Cable glanding Ø	7 - 12 mm
	Measures and weights	
	Weight	4.00 kg
	Dimension (W x H x D)	230 x 270 x 210
	Effective inside dimension (W)	210 mm
	Effective inside dimension (D)	195 mm
Effective inside dimension (H)	220 mm	
Fixing hole Ø	5.5 mm	
Accessory		
Front plate (optional)	-	