

Passive 10X Voltage Probe

TPP0051 Datasheet



TPP0051 Passive Voltage Probe

The TPP0051 probe is for use on BNC oscilloscopes with 1 M Ω /20 pF inputs.

Key performance specifications

- 10X attenuation
- 50 MHz bandwidth
- 1.3 m length
- UL61010-031; 2007, CAN/CSA C22.2 No. 61010-031-07, IEC61010-031; IEC 61010-031/A1:2008

Applications

- Low-frequency measurements
- Low-frequency computer and telecom measurements
- Power supplies
- Low-frequency amplifiers

Specifications

All specifications apply to all models unless noted otherwise.

Electrical characteristics

Bandwidth	DC to 50 MHz
Rise time	<7 ns (typical)
Compensation range	15 pF to 25 pF
Input resistance	10 M Ω \pm 1.5%
Input capacitance	<12 pF (typical)
Propagation delay	~6.1 ns
Maximum input voltage	300 V _{RMS} CAT II

Physical characteristics

Cable length	1.3 m (4.2 ft)
---------------------	----------------

EMC, environment, and safety

Temperature range	
Operating	10 °C to +55 °C (14 °F to 131 °F)
Nonoperating	-51 °C to +71 °C (-60 °F to 160 °F)
Operating and nonoperating	5% to 95% relative humidity (%RH) up to 30 °C (86 °F), 5% to 65% RH above +30 °C (86 °F) up to +55 °C (131 °F)
Altitude	
Operating	<3.0 km (9,842 ft)
Nonoperating	<12.2 km (40,026 ft)

Ordering information

Models

TPP0051 For use with BNC oscilloscopes with 1 M Ω , 20 pF inputs

Standard accessories

003-1433-xx	Adjustment tool
013-0362-xx	Retractable hook tip
016-0633-xx	Color bands, 5 pairs
016-2028-xx	Long ground spring, 2 each
196-3521-xx	6 in. alligator ground lead

Warranty

One-year warranty covering all parts and labor.

Recommended accessories

013-0363-xx	Micro hook tip
013-0366-xx	Universal IC cap
013-0367-xx	BNC-to-probe tip adapter, unterminated
016-2016-xx	PCB-to-probe tip adapter, 10-pack
016-2034-xx	Short ground spring, 2 each
020-3045-xx	Wire, 32 AWG spool
131-8831-xx	Compact probe-tip chassis mount
196-3198-xx	6 in. clip-on ground lead with 0.025 in. pin receptacle
196-3512-xx	12 in. alligator ground
206-0569-xx	MicroCKT test tip



Tektronix is registered to ISO 9001 and ISO 14001 by SRI Quality System Registrar.

ASEAN / Australasia (65) 6356 3900
Belgium 00800 2255 4835*
Central East Europe and the Baltics +41 52 675 3777
Finland +41 52 675 3777
Hong Kong 400 820 5835
Japan 81 (3) 6714 3010
Middle East, Asia, and North Africa +41 52 675 3777
People's Republic of China 400 820 5835
Republic of Korea 001 800 8255 2835
Spain 00800 2255 4835*
Taiwan 886 (2) 2722 9622

Austria 00800 2255 4835*
Brazil +55 (11) 3759 7627
Central Europe & Greece +41 52 675 3777
France 00800 2255 4835*
India 000 800 650 1835
Luxembourg +41 52 675 3777
The Netherlands 00800 2255 4835*
Poland +41 52 675 3777
Russia & CIS +7 (495) 6647564
Sweden 00800 2255 4835*
United Kingdom & Ireland 00800 2255 4835*

Balkans, Israel, South Africa and other ISE Countries +41 52 675 3777
Canada 1 800 833 9200
Denmark +45 80 88 1401
Germany 00800 2255 4835*
Italy 00800 2255 4835*
Mexico, Central/South America & Caribbean 52 (55) 56 04 50 90
Norway 800 16098
Portugal 80 08 12370
South Africa +41 52 675 3777
Switzerland 00800 2255 4835*
USA 1 800 833 9200

* European toll-free number. If not accessible, call: +41 52 675 3777

Updated 10 April 2013

For Further Information. Tektronix maintains a comprehensive, constantly expanding collection of application notes, technical briefs and other resources to help engineers working on the cutting edge of technology. Please visit www.tektronix.com.

Copyright © Tektronix, Inc. All rights reserved. Tektronix products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX and TEK are registered trademarks of Tektronix, Inc. All other trade names referenced are the service marks, trademarks, or registered trademarks of their respective companies.



03 Mar 2014

51W-30155-0

www.tektronix.com

