

Zarges GRP Platform Steps



The ideal Safety Steps for applications involving electrical hazards

- Glass reinforced polyester stiles: effective insulation and eliminated spark risk
- 80 mm deep aluminium alloy treads with non-slip serrated surface.
- Safety platform (approx. 250 mm x 250 mm).
- Safe storage of accessories and tools in an aluminium storage tray.
- Only 8.8 cm wide when folded - ideal for limited storage applications
- Standard: EN 131, 150 kilo rating

Product Code	No. of Treads	Closed Length (m)	Platform Height (m)	Base Width (m)	Base Spread (m)	Stile depth: front / back (mm)	Weight (kg)
40431 RS7990622	3	1.39	0.68	0.50	0.71	50 / 50	5.9
40432 RS7990629	4	1.64	0.91	0.52	0.87	50 / 50	6.9
40433 RS7990635	5	1.89	1.14	0.54	1.03	50 / 50	8.0
40434 RS7990626	6	2.14	1.37	0.57	1.20	50 / 50	9.4
40435 RS7990610	7	2.39	1.60	0.59	1.37	50 / 50	11.0