

# 3M Construction & Home Improvement Markets

## Product Information Sheet

### Command™ Adhesive Products



#### General Description


Command™ Adhesive is a high performance pressure sensitive foam tape designed with a unique, stretchable backing which allows clean, damage-free removal from most surfaces while having strong holding power on a wide variety of surfaces. The adhesive strips are quick and easy to install without tools.

The Command™ Product Line includes hooks, hangers, and clips that are designed to work with the Command™ Adhesive Strips to meet decorating and organizing needs in the home or office.

<b>Strip Construction</b>	Foam Type	Polyethylene
	Adhesive Type	Rubber
	Average Thickness (Foam Only)	0.042 in
	Color	White
	Release Liner	0.003 inch, red and black printed paper
	Approximate Foam Density	12 lb/ft <sup>3</sup> (192 kg/cm <sup>3</sup> )

<b>Typical Physical Properties and Performance Characteristics</b>	<b>Note:</b> The following technical information and data should be considered representative or typical only and should not be used for specification purposes.	
	<b>Peel Adhesion</b> (ASTM D-3330)	6 lbs/in width (58 N/100mm)
	<b>Static Shear Strength</b> (ASTM D-3654)	1000 g at 72°F (22°C)
	<b>Dynamic Shear</b> (ASTM D-1002)	100 lbs. (45 kg)
	<b>Temperature Resistance</b>	15°F to 120°F (-10°C to 50°C)
	<b>U.V. Resistance</b>	Not recommended for direct exposure to U.V. light
	<b>Solvent Resistance</b>	No apparent degradation when exposed to splash testing of most hydrocarbon solvents
	<b>Shelf Life</b>	24 months from the date of manufacture when stored in original cartons at 70°F (21°C) and 50% relative humidity

Available Sizes	Strip Width & Length	Tab Length	Adhesive Width & Length (Wall Side)	Adhesive Width & Length (Object Side)
Mini	0.50" x 1.177" (1.27 cm x 2.99 cm)	0.55" (1.40 cm)	0.50" x 0.61" (1.27 cm x 1.55 cm)	0.50" x 0.61" (1.27 cm x 1.55 cm)
Small	0.625" x 1.813" (1.58 cm x 4.60 cm)	0.75" (1.90 cm)	0.625" x 1.06" (1.58 cm x 2.69 cm)	0.625" x 0.857" (1.58 cm x 2.17 cm)
Medium	0.625" x 2.750" (1.58 cm x 6.98 cm)	0.75" (1.90 cm)	0.625" x 2.00" (1.58 cm x 5.08 cm)	0.625" x 1.797" (1.58 cm x 4.56 cm)
Large	0.75" x 3.650" (1.90 cm x 9.27 cm)	0.75" (1.90 cm)	0.75" x 2.90" (1.90 cm x 7.36 cm)	0.75" x 2.697" (1.90 cm x 6.85 cm)



Feature	Advantage	Benefit
Pressure-Sensitive Adhesive Strips	High adhesion	Excellent holding power
	Broad adhesion	Adheres to a wide variety of surfaces
	Quick and easy to install	No tools required
Stretch-Release Technology	Easy removal	Removes cleanly from most surfaces without damage
Foam Backing	Conformable	Adheres to both smooth and semi-rough surfaces
Hooks	Molded plastic utility and decorative styles	Designed to hold items ranging in weight from 0.5 – 7.5 lbs.
Hangers	Holds molded plastic, saw tooth, and wire-backed items	Holds pictures up to 5 lbs.
Clips	Molded plastic latch design	Securely holds items with diameters up to ½".

## To Mount:

1. To obtain optimum adhesion, the bonding surface must be clean and dry. Clean surface with isopropyl rubbing alcohol, wipe gently and let dry. Do not use household cleaners.
2. Separate the strips and remove the red liner. Press adhesive to back of hook or clip.
3. Remove black liner. Press the hook to the surface firmly for 10 seconds.
4. For hooks with a separate back plate, slide the hook up to remove from the back plate.
5. Press the back plate firmly for 30 seconds. Bond strength will depend upon the amount of adhesive-to-surface contact developed.
6. Slide the hook back onto the back plate.
7. Wait one hour before hanging items.

## To Remove:

1. Slide the hook up to remove it from the back plate.
2. Hold the top of the back plate gently against the surface.
3. Grab removal tab and SLOWLY stretch straight down along the wall at least 12 inches until the back plate and the strip release from the surface. NEVER pull the strip towards you.

## Notes:

- Failure to follow instructions carefully may result in damage
- Do not use with wallpaper
- May not adhere well to vinyl surfaces
- DO NOT use for antiques, heirlooms, or other valuable or irreplaceable items
- DO NOT hang objects over beds
- Use only one hook per item hung
- Apply to surfaces above 50° F (10° C)
- Adhesive could soften and lose adhesion above 105° F (40° C)
- Not for use in direct sunlight
- Not for use in wet environments
- Will not adhere to dirty, dusty, or oily surfaces
- Wait at least 7 days to apply to freshly painted surfaces
- Not recommended for use on bare wood or porous, unpainted surfaces
- Holding capacity is reduced if the load is applied less than one hour after the adhesive has been applied

Call 1-800-934-7355 or 1-800-3M HELPS (1-800-364-3577) for technical service assistance and additional information.

**3M Construction and Home Improvement Markets Division**  
3M Center, Building 251-1C-09  
St. Paul, MN 55144-1000

**IMPORTANT NOTICE:** All statements, technical information and recommendations herein are based on tests 3M believes to be reliable. 3M does not warrant or guarantee the accuracy or completeness of this information. THE FOLLOWING IS MADE IN LIEU OF ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE: 3M's only obligation shall be to replace such quantity of this 3M product proved to be defective. User is responsible for determining whether this 3M product is fit for a particular purpose and suitable for user's method of application. Because there are many factors that can affect the use and performance of this product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate this product to determine whether it is fit for a particular purpose, is suitable for the user's method of application, and meets the user's performance specifications and expectations.

**Limitation of Liability:** 3M SHALL NOT BE LIABLE FOR ANY LOSS OR DAMAGES, WHETHER DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL (INCLUDING BUT NOT LIMITED TO LOST PROFITS, BUSINESS, OR REVENUES) ARISING OUT OF THE USE OF OR INABILITY TO USE THIS 3M PRODUCT, WARRANTY, OR STRICT LIABILITY. No statement or recommendation not contained herein shall have any force or effect unless contained in an agreement signed by a 3M officer..