

88 01 300

KNIPEX Alligator® Water Pump Pliers



- more output and comfort compared to conventional water pump pliers of the same length: 9-notch adjustment positioning for 30 % more gripping capacity
- good access to the workpiece due to slim size of head and joint area
- self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- box-joint design: high stability due to double guide
- robust construction, insensitive to dirt; particularly suitable for outdoor work
- guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, oil-hardened



Article No.	88 01 300
EAN	4003773034094
Pliers	black atramentized
Head	polished
Handles	with non-slip plastic coating
Adjustment positions	9
Nominal size	300 mm
Capacities for pipes Ø Inch	2 3/4
Capacities for nuts mm	60
Capacities for pipes Ø mm	70
Length mm	300
Net weight g	511



Self-locking on pipes and nuts: no slipping on the workpiece; the complete actuating force can be used to turn the workpieces; not having to squeeze the pliers handles reduces the required effort



technical change and errors excepted



Spare Parts

Article No.	EAN	
88 09 300	4003773053521	Bolt (Kerpin) for 88 300