



fitted with

work equipment
 connected load
 power consumption
 glare-free
 system of protection
 class of protection
 usage
 luminaire body
 lamp cover
 tubular sections
 weight (net)
 mains lead

fastening

special features

1 x LED module
 light colour daylight white, 5300-6000 K, Color Rendering Index (CRI)=75
 Energy efficiency category A+
 electronic transformer
 95-240V; 50/60 Hz
 approx. 3 W
 without
 IP 20 (67)
 II
 without switch
 aluminium, anodised, Jet black
 glass screen
 Jet black
 approx. 1.1 kg
 approx. 3.0 m; mains plug
 CEE 7/XVI
 screw-down flange, table clamp (accessory), wall bracket (accessory)
 Flood with 25° angle of reflected beam



CEE 7/XVI

illuminance

measuring conditions: d=50cm; l=700mA

Em: 691 lx
 Emax: 1260 lx
 Emin: 221 lx

