



**fitted with**

**work equipment**

- connected load**
- power consumption**
- glare-free**
- system of protection**
- class of protection**
- usage**
- luminaire body**
- tubular sections**
- balance of articulation joints**
- weight (net)**
- mains lead**

**fastening**

- 1 x compact fluorescent lamp TC-LEL 36W/840 2G11
- light colour neutral white, 4000 K, Color Rendering Index (CRI)=80
- Energy efficiency category A
- conventional ballast
- Energy efficiency index (EEI): B1
- 230 V/ 50 Hz
- approx. 43 W
- aluminiumised parabolic louvre
- IP 20
- I
- switch
- plastic, light grey
- steel tube, painted, light grey
- spring
- approx. 3.7 kg
- approx. 1.5 m; mains plug
- CEE 7/II
- screw-down flange, table base (accessory), table clamp (accessory), wall bracket (accessory)



CEE 7/II

**illuminance**

measuring conditions: d=50cm

Em: 933 lx  
 Emax: 2010 lx  
 Emin: 217 lx

