



fitted with
work equipment
connected load
power consumption
light distribution
system of protection
class of protection
luminaire body
weight (net)
mains supply

fastening
dimension
light output
outside diameter
side part

1 x regular fluorescent lamp T26 36W/640 G13
 light colour neutral white
 electronic ballast
 Energy efficiency index (EEI): A2
 220-240V; 50/60Hz
 approx. 36 W
 direct
 IP 67
 I
 acrylic (PMMA), clear,
 approx. 3.7 kg
 connection box
 160 BU/3
 lamp bracket (accessory)
 A=1724 mm
 D=1200 mm
 70 mm
 C with screwed cable gland



160 BU/3

illuminance

Comment: d=100cm

Em: 410 lx
 Emax: 490 lx
 Emin: 303 lx

