



<b>DATA SHEET</b>	53112686
<b>SKINTOP® CLICK / CLICK-R</b>	valid from : 07.12.2012

The polyamide-based SKINTOP® CLICK / CLICK-R with its Snap-system enables a very fast and easy assembly and the integral locking features guarantees permanent vibration resistance. It is designed for use, above all for particular functional safety in manufacturing of machines and equipment, in measuring, controlling and automation, in electronic technology, switch cabinet technology.



### Components:

Body:	polyamide based plastic (UL 94- V2)
Cup nut:	polyamide based plastic (UL 94- V2)
Seal insert:	elastomer
Pressure nut:	polyamide based plastic, fibre-glass reinforced (UL 94- V2)
Flat seating ring:	elastomer/thermoplastic for size Ø 12, Ø 16, Ø 20, Ø 25
O-Ring:	NBR for size Ø 32

### Technical features:

Sizes:	Ø 12, Ø 16, Ø 20, Ø 25, Ø 32
Functional thread:	multi- start trapezoidal thread
Protection class:	IP 68, 5 - bar
Temperature range:	-20°C up to +100°C
Type construction:	CLICK = standard CLICK-R = standard with reducing seal insert
Colour RAL:	7035, 7001; 9005 UV-resistant in acc. to ISO 4892-2:2006, method A

### Approval:



### Norm references:



For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: M. Steinberg	document: DB53112686_7EN	page 1 von 1
---------------------------------------	--------------------------	--------------