

**Professionally approved products.**

## Datasheet

# Centre Lock Magnetic Clamp Base

RS Stock number [248-9045](#)



### Description:

A mechanical clamp fitted to a Noga centre lock arm, creates a universal method of mounting dial test indicators on to machinery, without the need for clean ferrous or flat areas. Will find numerous applications in machine shop or automotive applications (eg. disc brake run-out, etc.).

### Base:

Mechanical Clamp:

Capacity 75 mm round/square tube or flat plate

### Stand:

The pillar and arm are of lengths 160 and 110 mm respectively.

They are chrome plated steel and incorporates spherical knuckle joints top and bottom with centre lock assembly.

The fine adjustment is located at the head of the stand.

The clamp will accept dovetail lever gauges or 8 mm stem dial indicators.