



TD46GT - Closed End

General Part Information	
Product Description	TD46GT
Article Number	82067.00
Rivet Type	<input type="checkbox"/> i Closed End
Standard Bulk Pack Quantity	10000.00
Application / Features	<input type="checkbox"/> i  



Geometry / Dimensions / Performance	
Head Style	<input type="checkbox"/> i Domed
Body Diameter Ø (mm)	3.20
Body Length (mm)	9.70
Min. Grip Range (mm)	3.20
Max. Grip Range (mm)	4.80
Min. Hole Diameter (mm)	3.30
Max. Hole Diameter (mm)	3.40
Min. Flange Diameter (mm)	6.12
Max. Flange Diameter (mm)	6.65
Flange Thickness (mm)	0.87
Mandrel Diameter (mm)	2.00
Nominal Shear Strength (N)	2100.00
Nominal Tensile Strength (N)	2220.00

Material / Finish / Weight	
Body Material	<input type="checkbox"/> i Stainless Steel
Mandrel Material	Stainless Steel
Finish	Clean
Weight per thousand (kg)	1.47