

Mandatory sign - PML-M100 (D100)R - 1014181

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Mandatory sign, Roll, blue, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK X: Blank, Mounting type: Adhesive, Diameter: 100 mm, Lettering field: d: 100 mm

Why buy this product

- Stick-on mandatory signs, color preprinted, without symbol
- Suitable for indoor and outdoor use
- The mandatory signs conform to the ISO 7010 international standard
- Highly flexible, plasticized PVC labels which are ideal for uneven surfaces



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 784214
Weight per Piece (excluding packing)	99.99 g
Custom tariff number	39199000
Country of origin	Germany

Technical data

Dimensions

Width (a)	100 mm
Diameter	100.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
---------------------------------	------------------

General

Color	blue
Type	Round
Components	Silicone-free
Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	Blank

Mandatory sign - PML-M100 (D100)R - 1014181

Technical data

General

Number of individual labels	250
Marking mounting type	Adhesive

Classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27371301
eCl@ss 5.1	27371301
eCl@ss 6.0	27371301
eCl@ss 7.0	27371301
eCl@ss 8.0	27141137

ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC002498
ETIM 5.0	EC001777

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43212107

Accessories

Accessories

Ink ribbon

Ink ribbon - TM-RIBBON 110-TC/TR WH - 1014402



Ink ribbon, Length: 240000 mm, Color: white