

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [84508-0001](#)
Status: **Active**
Overview: XRC™ (Extra Rugged Circular) Sealed Plugs and Receptacles
Description: XRC™ Sealed Receptacle with Socket Insert, Shell Size 18, 14 Circuits, Blue Ring

Documents:

[Drawing \(PDF\)](#) [Application Specification AS-84501-001 \(PDF\)](#)
[Product Specification PS-84501-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152602

General

Product Family	Crimp Housings
Series	84508
Application	Power, Wire-to-Wire
Comments	84502-0004 Hex Nut For Panel Mounting Sold Separately. IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Conn
MolexKits	Yes
More Detailed Tech Information Overview	Extra thin wall wire seals XRC™ (Extra Rugged Circular) Sealed Plugs and Receptacles
Product Name	XRC™
UPC	822350758550

Physical

Circuits (maximum)	14
Flammability	94V-0
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Net Weight	42.502/g
Number of Rows	0
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	N/A
Pitch - Termination Interface	N/A
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-55°C to +125°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-84501-001
Product Specification	PS-84501-001
Sales Drawing	SD-84508-001



image - Reference only

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[84508Series](#)

Mates With

[84501](#) Plug

Use With

[84525](#) XRC™ Sealed Terminal Socket

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION