

TWO-HAND OPERATION CONSOLE FOR COMMAND DEVICES, 22MM, ROUND, ENCLOSURE MATERIAL METAL, ENCLOSURE TOP PART GRAY, 3 COMMAND POINTS METAL, STANDARD EQUIPMENT: 2 MUSHROOM PUSHB. BLACK 40MM, 2 X 1NO+1NC, SCREW TERMINAL, 1 EMERG. STOP RED, 40MM, 2NC, SCREW TERMINAL,



Figure similar

product brand name		SIRIUS ACT
Product designation		Commanding and signaling devices
Design of the product		Enclosure
Manufacturer article number		
<ul style="list-style-type: none"> of supplied contact module 		R2 = 3SU1400-1AA10-1BA0 / L2 = 3SU1400-1AA10-1BA0 / M1 = 3SU1400-1AA10-1CA0 / R1 = 3SU1400-1AA10-1CA0 / L1 = 3SU1400-1AA10-1CA0 / M2 = 3SU1400-1AA10-1CA0

Enclosure:		
Design of the housing		Two-hand operating console with standard components
Material of the enclosure		metal
Number of control points		3
Color		
<ul style="list-style-type: none"> of top part of the enclosure 		grey
Delivery state		
<ul style="list-style-type: none"> as a kit pre-wired on strip terminal 		No No
Mounting type of the enclosure		Horizontal

Actuator:		
Design of the operating mechanism		A = Mushroom pushbutton / B = Emergency stop mushroom pushbutton / C = Mushroom pushbutton
Manner of function of the actuating element		A = momentary contact / B = latching / C = momentary contact
Product feature		
<ul style="list-style-type: none"> lockout 		No

<ul style="list-style-type: none"> staggered switching 		No
Color		
<ul style="list-style-type: none"> of the actuating element 		A = black / B = red / C = black
Material of the actuating element		metal
Shape of the actuating element		round
Number of contact modules		6
Type of unlocking device		A = none / B = rotate to unlock / C = none

Front ring:		
Product component front ring		Yes
Material of the front ring		metal
Color of the front ring		silver

Holder:		
Material of the holder		Metal

General technical data:		
Product function		
<ul style="list-style-type: none"> positive opening 		Yes
<ul style="list-style-type: none"> EMERGENCY OFF function 		Yes
<ul style="list-style-type: none"> EMERGENCY STOP function 		Yes
Product component		
<ul style="list-style-type: none"> Stand/pedestal 		No
Vibration resistance		
<ul style="list-style-type: none"> acc. to IEC 60068-2-6 		10 ... 500 Hz: 5g
Protection class IP		IP66
Equipment marking		
<ul style="list-style-type: none"> acc. to DIN EN 61346-2 		S
<ul style="list-style-type: none"> acc. to DIN EN 81346-2 		S

Auxiliary circuit:		
Number of NC contacts		
<ul style="list-style-type: none"> for auxiliary contacts 		4
Number of NO contacts		
<ul style="list-style-type: none"> for auxiliary contacts 		2
Number of CO contacts		
<ul style="list-style-type: none"> for auxiliary contacts 		0
Design of the contact of the auxiliary contacts		Silver alloy

Connections/ Terminals:		
Type of electrical connection on enclosure		Cable routing at the rear 2 x M25

Ambient conditions:		
Ambient temperature		
<ul style="list-style-type: none"> during operation 	°C	-25 ... +70
<ul style="list-style-type: none"> during storage 	°C	-40 ... +80

Installation/ mounting/ dimensions:

Mounting type		Front plate mounting
• of modules and accessories		
Height	mm	183
Width	mm	493
Depth	mm	160

Accessories:

Number of backing plates		1
Marking of backing plate		EMERGENCY-STOP
Color of backing plate		Yellow

Certificates/ approvals:

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator




<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU18533NB001AA1>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SU18533NB001AA1/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU18533NB001AA1&lang=en





SIEMENS	3SU18.3.NB0_01_4_IEC.DXF <small>Format / Size: Hybrid que</small>
---------	--

last modified:

09.03.2015