



OUR OFFER

SIEMENS – SINAMICS G120

SINAMICS G120 - The modular converter – space-saving, safe and robust

Please select the Power Module (PU)

Stock-No.	Siemens MPN	Description
704-3865	6SL3224-0BE13-7UA0	PM240 0.37 kW
704-3874	6SL3224-0BE15-5UA0	PM240 0.55 kW
704-3877	6SL3224-0BE17-5UA0	PM240 0.75 kW
704-3880	6SL3224-0BE21-5UA0	PM240 1.5 kW
704-3887	6SL3224-0BE23-0UA0	PM240 3 kW
704-3896	6SL3224-0BE24-0UA0	PM240 4 kW
704-3903	6SL3224-0BE31-1UA0	PM240 11 kW
704-3906	6SL3224-0BE31-5UA0	PM240 15 kW
704-3900	6SL3224-0BE31-8UA0	PM240 18,5 kW
704-3919	6SL3224-0BE32-2UA0	PM240 22 kW



Please select the Control Unit (CU)

Stock-No.	Siemens MPN	Description
793-2128	6SL3244-0BB00-1BA1	CU240B-2 => CU with USS and Modbus RTU
793-2121	6SL3244-0BB00-1PA1	CU240B-2 DP => CU with Profibus DP
793-2125	6SL3244-0BB12-1BA1	CU240E-2 => CU with USS and Modbus RTU and Basic Safety Functions (STO)
793-2134	6SL3244-0BB12-1PA1	CU240E-2 DP => CU with Profibus DP and Basic Safety Functions (STO)



Please select optional components

Stock-No.	Siemens MPN	Description
744-9626	6SL3255-0AA00-4CA1	Basic Operator Panel
744-9629	6SL3255-0AA00-4JA1	Intelligent Operator Panel
744-9617	6SL3255-0AA00-2CA0	PC-Converter Connection Kit for CU's
793-2128	6SL3254-0AM00-0AA0	MMC Parameter Storage



For more technical information please visit:

www.rs-online.com