




Compact Thermal Printer

Ap1310DC

In-vehicle Printer



**Unique single-handed
easy paper load system**
No other printer is easier!

Typical applications include:

- Couriers
- Taxi receipts
- Emergency services
- Logistics

POWERFUL YET COMPACT

- Designed for easy and seamless vehicle installation with single cable integration
- 38 meters of printing per paper roll reducing paper changes and minimising maintenance for operational efficiencies
- Range of mounting brackets and options to suit a wide variety of in-vehicle uses
- Utilising a high speed and high quality fixed head thermal mechanism for superb quality prints
- Compact and quiet to reduce burden of in-vehicle printing



Head Office

(Design, Sales, Technical Support and Repair)

Able Systems Limited
Denton Drive
Northwich
Cheshire
CW9 7TU
England

Tel: +44 (0) 1606 48621

Fax: +44 (0) 1606 44903

Visit:

www.able-systems.com



www.able-systems.com


Thermal Portable Printer Ap1310DC
DATASHEET



Compact Thermal Printer

Ap1310DC

In-vehicle Printer



Specification	Ap1310DC	Ap1310DCBT
Data Input	RS-232 Serial (6-Core moulded cable)	RS-232 Serial (RJ12 connector)
Wireless Data Input	N/A	Bluetooth V2.1 (profiles: LM, L2CAP, RFCOMM, SDP, TCS, SSP, SPP and IAP. OPP optional)
Print Method	Fixed head thermal mechanism	
Print Speed	60 mm/s (with 12V input voltage)	
Paper Specification	Paper Roll Width: 57.0 ± 0.5mm. Max roll diameter: 55mm (approx. length: 33 metres) Accepts paper rolls with or without a core	
Print Width	48 mm	
Dots Per Line (Graphics)	384	
Dot Spacing	8 dots/mm (vertical and horizontal)	
Sensors	Paper Out (Opto reflective) and Head Up (Mechanical)	
Data Buffer	20 Kb	
Power Supply	9 VDC to 36 VDC continuous (integrated over-voltage protection). As standard the Ap1310DC is supplied with a moulded 6-core cable for both serial (RS232) and direct input voltage combined.	
Input Power	25 Watts Average (Typical while printing), 70 Watts (short term peak)	
Remote Shutdown	Apply >2V to shutdown pin to wake - Force Awake option available	
Baud Rate	Up to 57,600 (9600 Default)	
Character Set	IBM® 224 character set, CP437. (See note 1)	
Number Of Columns	12, 16, 21, 24, 42, 32 (Default). (See note 1)	
Font (Dots)	7 x 24, 10 x 24 (Default). (See note 1)	
Dimensions	65 x 95 x 128mm (H x W x L)	
Weight	Approx. 340g (including full roll of paper)	
Accessories	<ul style="list-style-type: none"> • Ap1300BR01: Combined wall mounting bracket and belt clip • Ap1300MBUG01: Universal gripper (mandatory for all mount choices) • Ap1300MB01: Self adhesive/screw mount • Ap1300MB02 /03: Tubular mounts (large/small) • Ap1300MB04 /05 /06: Suction mounts • Ap1300MBKIT1: Mounting bracket kit comprising all the above 	
Windows® Driver	Win98, WinME, WinNT, Win2k, WinXP, Vista and 7 (32 bit). Download: www.able-systems.com	
Temperature Range (operating)	0 - 50°C	
Reliability - MCBF	10 ⁸ print pulses or 50kms. >13 million print lines (Approx. 3,500 paper rolls).	

Note 1: The proprietary Font Editor Utility software (order code Ap800FEU) enables customisation of character fonts by the user.

Items are available individually or in the following kits:

Ap1310DCKIT1: comprising an Ap1310DC printer fitted with moulded 6-core cable for power and data (combined), an Ap1300BR01 belt clip/wall bracket and an A05856TPR1 paper roll.

YOUR LOCAL DISTRIBUTER:



E & OE. ©Copyright 2015 Able Systems Limited. All trade marks acknowledged. Specifications subject to change without notice. Ap1310DC/062015/V1

Thermal Portable Printer Ap1310DC
DATASHEET