

LED LENSER® i6

The LED Lenser i6 is perfect for penetrating less accessible locations that need plenty of light. Its longer barrel is ideal for illuminating narrow or confined spaces in workshops, factories and garages. The precise internal reflector lens is fitted with a CREE® Power LED Light Chip which employs the patented Advanced Focus System to shine bright, homogenous white light all the way from flood to spot beam, and is capable of picking out a component or blemish some distance away with pinpoint accuracy. There is a choice of Power or Low Power light settings, providing everything from high-intensity illumination down to a softer light useful for reading maps or viewing diagrams. Single-hand Speed Focus and an easy-grip metal body make handling comfortable for extended use – though with a long maximum run time of 25 hours the i6 will work through the most arduous inspection tasks long after any engineer or inspector has hit the deck.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Stylish Pen-light torch
- CREE® Power LED Light Chip
- State-of-the-art, reliable German engineering
- Advanced Focus System (AFS). Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Speed Focus® (one-handed spot-to-flood beam)
- Dynamic Switch
- Power and Low Power light modes
- Pocket Clip
- Water-resistant (IPX4)
- Robust metal housing

Technical Information	Power	Low Power
Lumens	140	10
Beam Distance (meters)	120	30
Run Time (hours)	5	25
Size:	167x19mm Ø	
Weight:	75g	
Batteries:	3 x AAA	
Supplied with: Batteries, Pouch		

* Also compatible with AAA NiMH batteries (not supplied)

Code	Description	Unit Colour	Packaging	Barcode
5606	i6	Black	Box	4029113560603
RRP ex.vat £24.96 / incl.vat £29.95				