



OUR OFFER

Schneider Electric – TeSys GV2-ME

Circuit Breaker TeSys GV2-ME

- Enclosed DOL starters 3-pole
- Safety switch disconnectors
- Thermal-magnetic motor circuit breakers
- Screw- or Spring- Terminal Type
- With a module width of 45 mm

Applications

- DOL starting or stopping of motors
- Load breaking of the machine control circuit



Stock-No.	MPN	Current Range	Terminal Type
395-0346	GV2ME01	0.1 - 0.16 A	Screw
395-0324	GV2ME02	0.16 - 0.25 A	Screw
395-0318	GV2ME03	0.25 - 0.4 A	Screw
395-0302	GV2ME04	0.4 - 0.63 A	Screw
395-0295	GV2ME05	0.63 - 1 A	Screw
395-0289	GV2ME06	1 - 1.6 A	Screw
395-0267	GV2ME07	1.6 - 2.5 A	Screw
395-0251	GV2ME08	2.5 - 4 A	Screw
395-0245	GV2ME10	4 - 6.3 A	Screw
395-0239	GV2ME14	6 - 10 A	Screw
395-0223	GV2ME16	9 - 14 A	Screw
395-0217	GV2ME20	13 - 18 A	Screw
400-1439	GV2ME21	17 - 23 A	Screw
395-0201	GV2ME22	20 - 25 A	Screw
395-0194	GV2ME32	24 - 32 A	Screw

Stock-No.	MPN	Current Range	Terminal Type
413-1568	GV2ME053	0.63 - 1 A	Spring
413-1574	GV2ME063	1 - 1.6 A	Spring
413-1580	GV2ME073	1.6 - 2.5 A	Spring
413-1596	GV2ME083	2.5 - 4 A	Spring
413-1603	GV2ME103	4 - 6.3 A	Spring
413-1619	GV2ME143	6 - 10 A	Spring
413-1625	GV2ME163	9 - 14 A	Spring
413-1631	GV2ME203	13 - 18 A	Spring
413-1647	GV2ME213	17 - 23 A	Spring
413-1653	GV2ME223	20 - 25 A	Spring

For more technical information please visit:

www.rs-online.com