

Accessories

LED and filament bulbs



LED bulbs

Description	Rated Current mA	Wave-length nm	Luminance mcd	Catalog number	Weight oz.
LED bulbs continued					
Rated voltage 230 V, AC/DC service life 25 000 h					
Red	4	630	60	KA2-2231	0.18
Green	4	525	500	KA2-2232	0.18
Yellow	4	592	70	KA2-2233	0.18
Blue	4	470	220	KA2-2234	0.18
White	4	¹⁾	350	KA2-2235	0.18

Note: Care should be taken for DC supply where + and - must be correctly connected. This is marked X1 (+) and X2 (-) on the product.

Choose the same color on the LED as on the lamp cap.

¹⁾X=0.31, Y=0.32 according to the ICI Chromaticity Diagram.



Filament bulb

Rated voltage V	Rated current mA	Rated output W	Service life h	Luminance mcd	Catalog number	Weight oz.
Filament bulbs BA 9s base						
6	200	1.2	10 000	350	5911 086-11	0.071
12	100	1.2	10 000	230	5911 086-12	0.071
24	50	1.2	10 000	280	5911 086-13	0.071
30	40	1.2	10 000	250	5911 086-4	0.071
48	42	2	6 000	500	5911 086-5	0.071
60	20	1.2	5 000	190	5911 086-14	0.071
110	18	2	7 500	250	5911 086-7	0.071
130	15	2	7 500	120	5911 086-15	0.071

Note: Catalog number of current: AC/DC. A Lamp Changing Tool is required for changing Bulb.

Lamp changing tool

For LED and filament bulbs	KA1-8072	0.071
----------------------------	----------	-------



Lamp changing tool