



Heat Shrinkable Tubing 2:1 - PVC

LVR

LVR can be used for cable joints, low voltage bus bars and batteries.

Features and Benefits

- PVC heat shrinkable tubing
- Self-extinguishing
- Good chemical resistance and mechanical protection



LVR used for mechanical protection.



Detailed Information about Heatguns please refer to page 529.

MATERIAL	Flexible Polyvinyl Chloride, cadmium free (PVC)
Shrink Ratio	2:1
Operating Temperature	-30 °C to +105 °C
Minimum Shrink Temperature	+135 °C
Longitudinal change after shrinkage	+/-10 % max
Dielectric Strength	15 kV/mm according to IEC 243
Shelf life	12 Months max.
Stocking Temperature	+25 °C max.
Flammability	ASTM D2671
Specifications	UL224 105 °C 600V



TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Reel Length	Colour	Article-No.
LVR-2.4/1.2	2.4	1.2	0.40	250 m	Black (BK)	344-00240
LVR-3.2/1.6	3.2	1.6	0.40	250 m	Black (BK)	344-00320
LVR-4.8/2.4	4.8	2.4	0.50	250 m	Black (BK)	344-00480
LVR-6.4/3.2	6.4	3.2	0.60	250 m	Black (BK)	344-00640
LVR-9.5/4.8	9.5	4.8	0.60	125 m	Black (BK)	344-00950
LVR-12.7/6.4	12.7	6.4	0.70	75 m	Black (BK)	344-01270
LVR-19.1/9.5	19.0	9.5	0.80	100 m	Black (BK)	344-01900
LVR-25.4/12.7	25.4	12.7	1.00	100 m	Black (BK)	344-02540

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.