



iM3075

Large Case

Transport Case



Seven Press & Pull Latches

- Seven Press & Pull Latches
- Four Double-layered, Soft-grip Handles
- Four Double-layered, Soft-grip Handles
- Two Padlockable Hasps
- Two Padlockable Hasps
- In-line Wheels
- In-line Wheels
- Telescoping Handle
- Telescoping Handle
- Vortex® Valve
- Vortex® Valve
- Flush Powerful Hinges
- Flush Powerful Hinges
- Lightweight Strong HPX® Resin
- Lightweight Strong HPX® Resin
- Watertight
- Watertight
- Peli's limited lifetime guarantee**
- Peli's limited lifetime guarantee****Where applicable by law
- **Where applicable by law

CONFIGURATIONS

iM3075 - Standard

iM3075-X0000 - With No Foam

iM3075-X0002 - With With Padded Dividers

DIMENSIONS

Interior (L x W x D): 29.80 x 20.80" x 17.80 (75.7 x 52.8 x 45.2 cm)

Exterior (L x W x D): 33.30 x 24.40" x 19.30 (84.6 x 62 x 49 cm)

Lid Depth: 4.00"

Bottom Depth: 13.75"

Total Depth: 17.75"

Int Volume: 6.38 ft³

MATERIALS

Body: Injection Molded HPX® high performance resin

Latch: Valox - Polybutylene Terephthalate (PBT)

Latch (Alt): Xenoy - Polyester/Polycarbonate blend

O-Ring: Silicone Sponge

Pins: Stainless Steel

Pins (Alt): Aluminum

Foam: 1.3/1.35 polyester

Purge Body: Valox - Polybutylene Terephthalate (PBT)

Purge Body (Alt): Xenoy - Polyester/Polycarbonate blend

Purge Vent: Gortex membrane

Purge O-Ring: Buna-N, 50-60 Durometer Shore A

COLOURS



Black



OD Green

WEIGHT

Weight With Foam: 45.00 lbs

Weight Without Foam: 31.50 lbs

Buoyancy: 388.20 lbs

Master Pack Weight: 37.00 lbs

TEMPERATURE

Minimum Temperature: -20°

Maximum Temperature: 140°

CERTIFICATIONS

MIL-STD-810F

ATA 300

FED-STD-101C

FOAM PROPERTIES

Layer 1 (Lid): 3.88" Convolute

Layer 2 (Base): 1.08" Pad

Layer 3 (Base): 1.75" Pick N Pluck

Layer 4 (Base): 3.00" Pick N Pluck

Layer 5 (Base): 3.00" Pick N Pluck

Layer 6 (Base): 3.00" Pick N Pluck

Layer 7 (Base): 3.00" Pick N Pluck

OTHER

Extendable Handle: yes

Master Pack: 1

Military: yes

Peli Products, S.L.U.

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999

info@peli.com • www.peli.com