

LEDLENSER iSEO5R

The Ledlenser iSEO5R is a high-quality rechargeable head lamp that has been precision engineered to meet the needs of professionals in the most testing of workplace and industrial environments. The recharging facility prolongs battery life and is sure to be welcomed by green advocates and company accountants alike. For users the iSEO5R is the perfect light choice when hands need to be kept free for important work. It is simple to operate with single front switch from which three Smart Light Technology light options can be selected: Power, Low Power and Blink. The premium Power LED will light up to 120 metres at 180 lumens, using patented Advanced Focus System optics to maintain even white light for both flood (near) and spot (distance) viewing. A simple turn of the light head focuses the light as desired. Also integrated is a handy red LED option, which makes for comfortable, dazzle-free viewing of diagrams and plans in low-light conditions as well as helping to preserve night vision. The lamp head can be tilted 60 degrees to save neck strain and help highlight harder-to-view corners and dark spots. A replaceable, machine washable head band makes the iSEO5R comfortable and clean to wear over sustained periods, while a Transport Lock prevents it from turning on when not in use and stops accidental battery drain. The iSEO5R is IPX6 rated for superior protection against water ingress. Supplied with 1 x L-ion Rechargeable Battery Pack, USB charging cable, Helmet Connecting kit and protective storage pouch. Will also work with 3xAAA standard alkaline batteries (not supplied)

As a leading international brand of hand-held torches and head lamps, Ledlenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, Ledlenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. Ledlenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient premium LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Rechargeable Head Torch
- Premium Power LED (white light) + glare-free LED (red light)
- Advanced Focus System (AFS). Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Smart Light Technology – Power, Low Power, Blink
- Instant Focusing – Focus the light with just one twist
- Transport Lock – to prevent accidental battery drain
- Lamp head swivels 60°
- Water-resistant (IPX6)
- Supplied with: Helmet Mount Kit, USB Cable, Helmet Clips, Pouch, 1 x L-ion Rechargeable Battery Pack

Technical Information

iSEO5R	BOOST	POWER	LOW POWER
POWER	x	180 lumens	20 lumens
BEAM DISTANCE	x	120 metres	40 metres
RUN TIME	x	10 hours	50 hours
SIZE	x	WEIGHT	105g

Supplied with: Helmet Mount Kit, USB Cable, Helmet Clips, Pouch, 1 x L-ion Rechargeable Battery Pack



* Will also work with 3xAAA alkaline batteries (not supplied)

Code	Description	Unit Colour	Packaging	Barcode
5605R	iSEO5R	Black/Yellow	Box	4029113560504