



ENGLISH

**Datasheet**

**Stock No: 199-725**

# **RS Pro 1.2V NiMH Tagged Terminal 1/3 AA NiMH Rechargeable Battery**



## **Product Details**

### **RS Pro, Standard Tagged**

Tagged to allow for combining into larger battery packs for permanent installation

Voltage 1.2V

Quick 4 to 6hr charging rate.

### **Note**

All batteries are supplied with only a residual charge and should be charged at the continuous charge rate before use.

### **Caution**

Do not connect batteries in parallel.

### **NiMH Rechargeable Industrial Batteries**

Improved performance over NiCd batteries.



## Specifications

Size	1/3 AA
Nominal Voltage	1.2V
Capacity	300mAh
Chemistry	NiMH
Dimensions	17 x 14.1mm
Terminal Type	Tagged
Maximum Continuous Current	3mA
Operating Temperature Range	-10 → +60°C
Maximum Operating Temperature	+60°C
Minimum Operating Temperature	-10°C